

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A4-80 M12X50

Article number	53510.120.050
Brand	-
UBB	950351832502
UNSPSC	31161620
EAN	8715492318091
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M12
Length	50 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
ASME	B18.2.3.1M
NEN	1555
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	50
P	1.75

Technical Drawing



