

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A4-80 M16X110

Article number	53510.160.110
Brand	-
UBB	500571357614
UNSPSC	31161620
EAN	8715494119313
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	110 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NF	E25-112
NEN	1555
DIN	931
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	110
P	2

Technical Drawing



