

ISO 4017 Fully Threaded Metric Hexagon Head Bolt, Stainless Steel A4 80 M10X55

Article number	53519.100.055
Brand	-
UBB	500697374550
UNSPSC	31161620
EAN	8715492956576
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	55 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	E25-114
ASME	B18.2.3.1M
ISO	4017
NEN	1568
DIN	933

Technical Specification

d-D	M10
k	6.4
L (mm)	55
P	1.5
s	16

Technical Drawing

