

Zeskanttapbout DIN 933 Roestvaststaal (RVS) A4 80 M10X35

Artikelnummer	53520.100.035
Merk	-
UBB	950351838475
UNSPSC	31161620
EAN	8715492318817
PKG. van 50	Alleen volledige verpakkingen

Technische parameters

Diameter	M10
Length	35 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Standaarden

NEN	1568
ASME	B18.2.3.1M
DIN	933
ISO	4017
NF	E25-114

Technische specificatie

d-D	M10
k	6.4
L (mm)	35
P	1.5
s	17

Technische tekening

