

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A4-70 M8X130

Article number	55000.080.130
Brand	-
UBB	951351769983
UNSPSC	31161620
EAN	8715492320353
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M8
Length	130 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Info Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NF	E25-112
NEN	1555
ISO	4014
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	130
P	1.25
s	13

Technical Drawing

