

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A4-70 M12X230

Article number 55000.120.230

Brand -

UBB 500571538973

UNSPSC 31161620

EAN 8715494120685

PKG. of 10 Full Box Only

Technical Parameters

Diameter	M12
Length	230 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
DIN	931
NF	E25-112
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	230
P	1.75

Technical Drawing



