

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A4-70 M20X70

Article number	55000.200.070
Brand	-
UBB	950351852716
UNSPSC	31161620
EAN	8715492321398
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	70 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

DIN	931
ISO	4014
NEN	1555
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	70
P	2.5

Technical Drawing



