

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A4-70 M36X240

Article number	55000.360.240
Brand	-
UBB	952351691904
UNSPSC	31161620
EAN	8715492322418
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M36
Length	240 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NEN	1555
NF	E25-112
ASME	B18.2.3.1M
ISO	4014
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	84
b (min.): L200mm	97
b (min.): L≤125mm	78
d-D	M36
k	22.5
L (mm)	240
P	4

Technical Drawing



