

DIN 933 Fully Threaded Metric Hexagon Head Bolt, Stainless Steel A4-70 M10X50

Article number	55010.100.050
Brand	-
UBB	950351863457
UNSPSC	31161620
EAN	8715492324290
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	50 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NF	E25-114
ISO	4017
DIN	933
ASME	B18.2.3.1M
NEN	1568

Technical Specification

d-D	M10
k	6.4
L (mm)	50
P	1.5
s	17

Technical Drawing

