

DIN 933 Fully Threaded Metric Hexagon Head Bolt, Stainless Steel A4-70 M10X150

Article number	55010.100.150
Brand	-
UBB	500621795805
UNSPSC	31161620
EAN	8715494513340
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M10
Length	150 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Info
 Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4017
NEN	1568
NF	E25-114
DIN	933
ASME	B18.2.3.1M

Technical Specification

d-D	M10
k	6.4
L (mm)	150
P	1.5
s	17

Technical Drawing

