

## DIN 933 Fully Threaded Metric Hexagon Head Bolt, Stainless Steel A4-70 M12X120

|                |               |
|----------------|---------------|
| Article number | 55010.120.120 |
| Brand          | -             |
| UBB            | 951351916667  |
| UNSPSC         | 31161620      |
| EAN            | 8715492324597 |
| PKG. of 25     | Full Box Only |

### Technical Parameters

|                    |                                                                                      |
|--------------------|--------------------------------------------------------------------------------------|
| Diameter           | M12                                                                                  |
| Length             | 120 mm                                                                               |
| Class              | Min.50                                                                               |
| Driving features   | Hexagon                                                                              |
| Head shape         | Hexagon head                                                                         |
| Material           | Stainless steel                                                                      |
| Material technical | A4                                                                                   |
| Thread direction   | Right                                                                                |
| Thread             | Metric thread                                                                        |
| Info               | Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50. |

### Standards

|      |            |
|------|------------|
| NF   | E25-114    |
| DIN  | 933        |
| ISO  | 4017       |
| NEN  | 1568       |
| ASME | B18.2.3.1M |

### Technical Specification

|        |      |
|--------|------|
| d-D    | M12  |
| k      | 7.5  |
| L (mm) | 120  |
| P      | 1.75 |
| s      | 19   |

### Technical Drawing

