

DIN 933 Fully Threaded Metric Hexagon Head Bolt, Stainless Steel A4-70 M24X75

Article number	55010.240.075
Brand	-
UBB	500571378826
UNSPSC	31161620
EAN	8715494116077
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	75 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NF	E25-114
NEN	1568
DIN	933
ASME	B18.2.3.1M
ISO	4017

Technical Specification

d-D	M24
k	15
L (mm)	75
P	3
s	36

Technical Drawing

