



## Hexagon socket button head screw ISO 7380-1 Stainless steel A4 M6X80

Article number	55030.060.080
Brand	-
UBB	500633359269
UNSPSC	31161518
EAN	8715494618717
PKG. of 100	Full Box Only

### Technical Parameters

Diameter	M6
Length	80 mm
Driving features	Hexagon socket
Head shape	Button head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

### Standards

ASME	≈B18.3.4M
NF	≈E25-126
BS	≈4168-6
ISO	7380-1

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

Technical Specification

d-D	M6
dk (max.)	10.5
Full thread if $L \leq$	30
k (max.)	3.3
L (mm)	80
P	1
s	4

Technical Drawing

