



Hexagon socket button head screw ISO 7380-1 Stainless steel A4 M6X120

Article number	55030.060.120
Brand	-
UBB	500633359590
UNSPSC	31161518
EAN	8715494618748
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	120 mm
Driving features	Hexagon socket
Head shape	Button head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Standards

ISO	7380-1
NF	≈E25-126
ASME	≈B18.3.4M
BS	≈4168-6

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

Technical Specification

d-D	M6
dk (max.)	10.5
Full thread if $L \leq$	30
k (max.)	3.3
L (mm)	120
P	1
s	4

Technical Drawing

