



**Hexalobular socket button  
head screw ISO ≈7380-1  
Stainless steel A4 M6X10**

Article number	55032.060.010
Brand	-
UBB	500634458813
UNSPSC	31161518
EAN	8715494554589
PKG. of 500	Full Box Only

**Technical Parameters**

Diameter	M6
Length	10 mm
Driving features	Hexalobular
Head shape	Button head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

**Standards**

NF	≈E25-126
ISO	≈7380-1
BS	≈4168-6
ASME	≈B18.3.4M

Technical Specification

d-D	M6
dk (max.)	10.5
k (max.)	3.3
L (mm)	10
P	1
Socket	30

Technical Drawing

