



Hexagon socket head cap screw with low head DIN 7984 Stainless steel A4 M6X45

Article number	55040.060.045
Brand	-
UBB	500512317800
UNSPSC	31161605
EAN	8715494287807
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	45 mm
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

Standards

DIN	7984
-----	------

Technical Specification

b (min.)	18
d-D	M6
dk	10
Full thread if $L \leq$	25
k	4
L (mm)	45
P	1
s	4

Technical Drawing

