



Hexagon socket head cap screw DIN 912 Stainless steel A4 Min.50 M3X35

Article number	55050.030.035
Brand	-
UBB	951351811058
UNSPSC	31161605
EAN	8715492327727
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	35 mm
Class	Min.50
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

ISO	4762
NF	E25-125
ASME	B18.3.1M
BS	4168-1
NEN	1241
DIN	912

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if L ≤	20
k (max.)	3
L (mm)	35
P	0.5
s	2.5

Technical Drawing

