



Hexagon socket head cap screw DIN 912 Stainless steel A4 Min.50 M5X55

Article number	55050.050.055
Brand	-
UBB	950351874595
UNSPSC	31161605
EAN	8715492328007
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	55 mm
Class	Min.50
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

ASME	B18.3.1M
BS	4168-1
NEN	1241
ISO	4762
DIN	912
NF	E25-125

Technical Specification

b	22
d-D	M5
dk (max.)	8.5
Full thread if $L \leq$	25
k (max.)	5
L (mm)	55
P	0.8
s	4

Technical Drawing

