



Hexagon socket head cap screw DIN 912 Stainless steel A4 Min.50 M5X85

Article number	55050.050.085
Brand	-
UBB	500571290534
UNSPSC	31161605
EAN	8715494141314
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	85 mm
Class	Min.50
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

NEN	1241
ISO	4762
ASME	B18.3.1M
NF	E25-125
BS	4168-1
DIN	912

Technical Specification

b	22
d-D	M5
dk (max.)	8.5
Full thread if L ≤	25
k (max.)	5
L (mm)	85
P	0.8
s	4

Technical Drawing

