



Hexagon socket head cap screw DIN 912 Stainless steel A4 Min.50 M10X220

Article number	55050.100.220
Brand	-
UBB	500571293843
UNSPSC	31161605
EAN	8715494141642
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M10
Length	220 mm
Class	Min.50
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

NEN	1241
ISO	4762
BS	4168-1
DIN	912
NF	E25-125
ASME	B18.3.1M

Technical Specification

b	32
d-D	M10
dk (max.)	16
Full thread if L ≤	40
k (max.)	10
L (mm)	220
P	1.5
s	8

Technical Drawing

