



Hexagon socket head cap screw DIN 912 Stainless steel A4 70 M16X30

Article number	55050.160.030
Brand	-
UBB	950351880360
UNSPSC	31161605
EAN	8715492328991
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	30 mm
Class	70
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

DIN	912
NF	E25-125
ISO	4762
NEN	1241
ASME	B18.3.1M
BS	4168-1

Technical Specification

b	44
d-D	M16
dk (max.)	24
Full thread if L ≤	60
k (max.)	16
L (mm)	30
P	2
s	14

Technical Drawing

