



M10 DIN 976-1A Threaded Rod, Stainless Steel A4, 1m

Article number	55070.100.001
Brand	-
UBB	950353287564
UNSPSC	31161618
EAN	8715492332035
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M10
Length	1000 mm
Class	70
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M3 or M24 are minimal property class 50.1 meter

Standards

NF	E25-136
DIN	976-1A

Technical Specification

d-D	M10
L (mm)	1000
P	1.5

Technical Drawing

