



Hexagon socket set screw with dog point DIN 915 Stainless steel A4 M10X10

Article number	55230.100.010
Brand	-
UBB	500571744555
UNSPSC	31161518
EAN	8715494117777
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M10
Length	10 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A4
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

DIN	915
NEN	2344
NF	E27-182
ASME	B18.3.6M
ISO	4028
BS	4168-4

Technical Specification

d-D	M10
dp (max.)	7
L (mm)	10
P	1.5
s	5
t (min.)	4
z long (min.)	5
z long if L ≥	16
z short (min.)	2.5

Technical Drawing

