



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A4 M3X35

Article number	55302.030.035
Brand	-
UBB	500633407514
UNSPSC	31161504
EAN	8715494623551
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	35 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ISO	≈7046-1
NF	≈E25-119-1
DIN	965

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	35
No. cross recess	1
P	0.5

Technical Drawing

