



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A4 M5X80

Article number	55302.050.080
Brand	-
UBB	500633408439
UNSPSC	31161504
EAN	8715494623643
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	80 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-119-1
ISO	≈7046-1
DIN	965

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if L ≤	30
k (max.)	2.5
L (mm)	80
No. cross recess	2
P	0.8

Technical Drawing

