



Cross recessed countersunk head tapping screw Pozidriv DIN 7982 C-Z Stainless steel A4 ST4,8X38MM

Article number	55681.048.038
Brand	-
UBB	500634538283
UNSPSC	31161507
EAN	8715494556057
PKG. of 500	Full Box Only

Technical Parameters

Diameter	4.8 mm
Length	38 mm
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Self tapping thread

Standards

DIN	7982 CZ
NF	E25-656 C
ISO	7050 CZ

Technical Specification

D (mm)	4.8
dk	9.5
k ≈	3
L (mm)	38
No. cross recess	2
P	1.6

Technical Drawing

