



**Slotted cheese head screw
DIN 84 Plastic Polyamide
(nylon) 6.6 M5X6**

Article number	56410.050.006
Brand	-
UBB	950353539295
UNSPSC	31161504
EAN	8715492862723
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	6 mm
Class	6.6
Color	White
Driving features	Slotted
Head shape	Cylindrical head
Material	Plastic
Material technical	Polyamide (nylon)
Thread	Metric thread

Standards

NF	≈E25-127
BS	≈4183
ASME	≈B18.6.7M
ISO	≈1207
DIN	84
NEN	≈1602

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	8.5
Full thread if L ≤	40
k (max.)	3.3
L (mm)	6
n	1.2
P	0.8
t (min.)	1.3

Technical Drawing