



**Slotted cheese head screw
DIN 84 Plastic Polyamide
(nylon) 6.6 M5X12**

Article number	56410.050.012
Brand	-
UBB	950353319177
UNSPSC	31161504
EAN	8715492862754
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	12 mm
Class	6.6
Color	White
Driving features	Slotted
Head shape	Cylindrical head
Material	Plastic
Material technical	Polyamide (nylon)
Thread	Metric thread

Standards

NF	≈E25-127
DIN	84
ASME	≈B18.6.7M
BS	≈4183
ISO	≈1207
NEN	≈1602

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	8.5
Full thread if L ≤	40
k (max.)	3.3
L (mm)	12
n	1.2
P	0.8
t (min.)	1.3

Technical Drawing