



Slotted cheese head screw DIN 84 Plastic Polyamide (nylon) 6.6 M5X25

Article number	56410.050.025
Brand	-
UBB	950353319417
UNSPSC	31161504
EAN	8715492862792
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	25 mm
Class	6.6
Color	White
Driving features	Slotted
Head shape	Cylindrical head
Material	Plastic
Material technical	Polyamide (nylon)
Thread	Metric thread

Standards

BS	≈4183
DIN	84
NEN	≈1602
ISO	≈1207
NF	≈E25-127
ASME	≈B18.6.7M

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	8.5
Full thread if L ≤	40
k (max.)	3.3
L (mm)	25
n	1.2
P	0.8
t (min.)	1.3

Technical Drawing