



KIPP Clamping levers 20 degrees, external thread
Black Die cast zinc/steel 5.8
Plastic coated/black oxide
M12X25X30

Article number	58027.120.030
Brand	-
UBB	500689477668
UNSPSC	31162807
EAN	4059245079537
PKG. of 5	Full Box Only

Technical Parameters

Class	5.8
Color	Black
D1_MM	25mm
Material	Die cast zinc/steel
Surface treatment	Plastic coated/black oxide
Thread	Metric thread
Info	Material: Handle die-cast zinc EN 12844. Steel parts grade 5.8.Version: Handle plastic coated. Steel parts black oxidized.

Standards

Technical Specification

A	95
A1	108
D	19
D1	25
D2	26
D3	19
H	42.5
H2	26

Technical Drawing

H3	67
H4	72
H1	10
Number of teeth	24
L	30
X	12

FABORY

