



KIPP Clamping levers, external thread Orange Die cast zinc/steel 5.8 Plastic coated/black oxide M5X30X35

Article number	58042.050.035
Brand	-
UBB	500689531860
UNSPSC	31162807
EAN	4059245088720
PKG. of 10	Full Box Only

Technical Parameters

Class	5.8
Color	Orange
D1_MM	13mm
Material	Die cast zinc/steel
Surface treatment	Plastic coated/black oxide
Thread	Metric thread
Info	Material: Handle die-cast zinc EN 12844. Steel parts grade 5.8. Version: Handle plastic coated. Steel parts black oxidized. Drawing reference: 1) flat point DIN 78.

Standards

Technical Specification

A	30
A1	37
B	7
D	10
D1	13
D2	14

Technical Drawing

H	24.5
H2	14.5
H3	30
H4	33
H1	4
Number of teeth	16
L	35
X	5

