



KIPP Clamping levers, external thread Red Die cast zinc/steel 5.8 Plastic coated/ black oxide M12X95X35

Article number	58044.120.035
Brand	-
UBB	500689555125
UNSPSC	31162807
EAN	4059245093090
PKG. of 5	Full Box Only

Technical Parameters

Class	5.8
Color	Red
D1_MM	27mm
Material	Die cast zinc/steel
Surface treatment	Plastic coated/black oxide
Thread	Metric thread
Info	Material: Handle die-cast zinc EN 12844. Steel parts grade 5.8. Version: Handle plastic coated. Steel parts black oxidized. Drawing reference: 1) flat point DIN 78.

Standards

Technical Specification

A	95
A1	109
B	13
D	19
D1	27
D2	27.5
H	43

Technical Drawing

H2	27
H3	63
H4	67.5
H1	10
Number of teeth	24
L	35
X	12

