



KIPP Clamping levers, internal thread Chrome Die cast zinc/steel 5.8 High gloss chromed/black oxide M8X80

Article number	58047.080.080
Brand	-
UBB	500689573698
UNSPSC	31162807
EAN	4059245085132
PKG. of 5	Full Box Only

Technical Parameters

A	80
X	M8
Class	5.8
Color	Chrome
Material	Die cast zinc/steel
Surface treatment	High gloss chromed/ black oxide
Thread	Metric thread
Info	Material: Handle die- cast zinc EN 12844. Steel parts grade 5.8. Version: Handle high-gloss chromed. Steel parts black oxidized.

Standards

Technical Specification

A	80
A ₁	91
B	11
D	16
D ₁	21
D ₂	22
H	37

Technical Drawing

H2	24
H3	54.5
H4	58.5
H ₁	10
Number of teeth	22
T	14
X	M8

OF COURSE

SETTING THE STANDARD
IN FASTENING SOLUTIONS

