



KIPP Clamping levers, external thread with cap Orange Die cast zinc/steel 5.8 Plastic coated/black oxide M8X65X60

Article number	58052.080.060
Brand	-
UBB	500689595147
UNSPSC	31162807
EAN	4059245095032
PKG. of 5	Full Box Only

Technical Parameters

A	65
L	60
X	M8
Class	5.8
Color	Orange
Material	Die cast zinc/steel
Surface treatment	Plastic coated/black oxide
Thread	Metric thread

Info	Material: Handle die-cast zinc EN 12844. Steel parts grade 5.8. Protective cap stainless steel 1.4305. Version: Handle plastic coated. Steel parts black oxidized. Protective cap stainless steel, bright.
------	--

Standards

Technical Specification

A	65
A ₁	74.5

Technical Drawing

B	9.5
D	13.5
D ₁	18.5
D ₂	19
H	32
H ₂	17.5
H ₃	42.5
H ₄	45.5
H ₁	6.5
Number of teeth	20
X	M8

