



**KIPP Clamping levers,
external thread Black Die
cast zinc/stainless steel
1.4305 Plastic coated/bright
M6X65X15**

Article number	58054.061.015
Brand	-
UBB	500689601572
UNSPSC	31162807
EAN	4059245096596
PKG. of 5	Full Box Only

Technical Parameters

Color	Black
D1_MM	18.5mm
Material	Die cast zinc/ stainless steel
Material technical	1.4305
Surface treatment	Plastic coated/bright
Thread	Metric thread
Info	Material: Handle die- cast zinc EN 12844. Steel parts stainless steel 1.4305.Version: Handle plastic coated. Stainless steel bright.Drawing reference: 1) flat point DIN 78.

Standards

Technical Specification

A	65
A1	74.5
B	9.5
D	13.5
D1	18.5
D2	19

Technical Drawing

H	28.5
H2	17.5
H3	42.5
H4	45.5
H1	6.5
Number of teeth	20
L	15
X	6

