



KIPP Clamping levers, internal thread Silver Die cast zinc/stainless steel 1.4305 Plastic coated/bright M12X95

Article number	58059.120.095
Brand	-
UBB	500689621539
UNSPSC	31162807
EAN	4059245086054
PKG. of 3	Full Box Only

Technical Parameters

Color	Silver
D1_MM	27mm
Material	Die cast zinc/ stainless steel
Material technical	1.4305
Surface treatment	Plastic coated/bright
Thread	Metric thread
Info	Material: Handle die- cast zinc EN 12844. Steel parts stainless steel 1.4305.Version: Handle plastic coated. Stainless steel bright.

Standards

Technical Specification

A	95
A1	109
B	13
D	19
D1	27
D2	27.5
H	43

Technical Drawing

H2	27
H3	63
H4	67.5
H1	10
Number of teeth	24
T	17
X	12

