



**KIPP Clamping levers,
external thread Silver
Stainless steel 1.4308/1.4305
Electrolytic polished/bright
M6X40X40**

Article number	58068.060.040
Brand	-
UBB	500689644499
UNSPSC	31162807
EAN	4059245099375
PKG. of 2	Full Box Only

Technical Parameters

Color	Silver
D1_MM	13mm
Material	Stainless steel
Material technical	1.4308/1.4305
Surface treatment	Electrolytic polished/ bright
Thread	Metric thread
Info	Material: Handle investment cast 1.4308. Other steel parts 1.4305.Version: Handle electropolished. Metal parts bright.Drawing reference: 1) flat point DIN 78.

Standards

Technical Specification

A	40
A1	47
B	7
D	10
D1	13

Technical Drawing

D2	14
H	24.5
H2	14.5
H3	31
H4	34
H1	4
Number of teeth	16
L	40
X	6

