



KIPP Clamping levers, external thread with cap Silver Stainless steel 1.4308/1.4305 Electrolytic polished/bright M10X65X60

Article number	58070.100.060
Brand	-
UBB	500689651643
UNSPSC	31162807
EAN	4059245099993
PKG. of 2	Full Box Only

Technical Parameters

Color	Silver
D1_MM	18.5mm
Material	Stainless steel
Material technical	1.4308/1.4305
Surface treatment	Electrolytic polished/ bright
Thread	Metric thread
Info	Material: Handle investment cast 1.4308. Other steel parts 1.4305.Version: Handle electropolished. Steel parts bright.

Standards

Technical Specification

A	65
A1	74.5
B	9.5
D	13.5
D1	18.5
D2	19
H	32

Technical Drawing

H2	17.5
H3	42.5
H4	45.5
H1	6.5
Number of teeth	20
L	60
X	10

