



**KIPP Clamping levers**  
**2K, external thread Steel**  
**5.8/plastic Black oxide**  
**M5X40,1X20**

Article number	58072.050.020
Brand	-
UBB	500689653219
UNSPSC	31162807
EAN	4059245113644
PKG. of 10	Full Box Only

**Technical Parameters**

Class	5.8
D1_MM	15mm
Material	Steel/plastic
Surface treatment	Black Oxide
Thread	Metric thread

Info

Material: Handle:  
Hard component  
fibreglass reinforced  
plastic with die-cast  
zinc toothed ring.  
Soft component  
Thermoflex based on  
SEBS. Steel parts:  
grade 5.8.Version:  
Steel parts black  
oxidized.Note:  
The hard and soft  
components are  
supplied in black  
grey RAL 7021 as  
standard.

**Standards**

**Technical Specification**

A	40.1
A1	48.1
B	10.1
D	10

**Technical Drawing**

D1	15
D2	16
H	24.5
H2	10
H3	30
H4	33.5
H1	4
Number of teeth	16
L	20
X	5

