



KIPP Clamping levers plastic grip, external thread Signal green Steel 5.8/plastic Black oxide M5X40X25

| | |
|----------------|---------------|
| Article number | 58096.050.025 |
| Brand | - |
| UBB | 500689699923 |
| UNSPSC | 31162807 |
| EAN | 4059245103829 |
| PKG. of 10 | Full Box Only |

Technical Parameters

| | |
|-------------------|--|
| Class | 5.8 |
| Color | Signal green |
| D1_MM | 13mm |
| Material | Steel/plastic |
| Surface treatment | Black Oxide |
| Thread | Metric thread |
| Info | For many people the Novo-Grip clamping lever represents the key to secure and comfortable gripping. This lever provides a future-oriented and powerful solution for almost any operating and clamping problem.Material: Handle fibreglass reinforced plastic with die-cast zinc toothed ring. Steel parts grade 5.8.Version: Steel parts black oxidized. |

Standards

Technical Specification

| | |
|---|----|
| A | 40 |
|---|----|

Technical Drawing

| | |
|-----------------|------|
| A1 | 47 |
| B | 7.5 |
| D | 10 |
| D1 | 13 |
| D2 | 14.5 |
| H | 24.5 |
| H2 | 15 |
| H3 | 30 |
| H4 | 33.5 |
| H1 | 4 |
| Number of teeth | 16 |
| L | 25 |
| X | 5 |

