



KIPP Clamping levers plastic grip, external thread Signal green Steel 5.8/plastic Black oxide M12X95X45

Article number	58096.120.045
Brand	-
UBB	500689708187
UNSPSC	31162807
EAN	4059245108763
PKG. of 5	Full Box Only

Technical Parameters

Class	5.8
Color	Signal green
D1_MM	25.5mm
Material	Steel/plastic
Surface treatment	Black Oxide
Thread	Metric thread

Info	For many people the Novo-Grip clamping lever represents the key to secure and comfortable gripping. This lever provides a future-oriented and powerful solution for almost any operating and clamping problem. Material: Handle fibreglass reinforced plastic with die-cast zinc toothed ring. Steel parts grade 5.8. Version: Steel parts black oxidized.
------	--

Standards

Technical Specification

A	95
---	----

Technical Drawing

A1	109
B	13
D	19
D1	25.5
D2	27.5
H	43
H2	26
H3	61
H4	66
H1	10
Number of teeth	24
L	45
X	12

