



KIPP Clamping levers plastic grip, external thread Traffic blue Steel 5.8/plastic Black oxide M6X40X45

Article number	58102.060.045
Brand	-
UBB	500689738796
UNSPSC	31162807
EAN	4059245104499
PKG. of 10	Full Box Only

Technical Parameters

Class	5.8
Color	Traffic blue
D1_MM	13mm
Material	Steel/plastic
Surface treatment	Black Oxide
Thread	Metric thread
Info	For many people the Novo-Grip clamping lever represents the key to secure and comfortable gripping. This lever provides a future-oriented and powerful solution for almost any operating and clamping problem. Material: Handle fibreglass reinforced plastic with die-cast zinc toothed ring. Steel parts grade 5.8. Version: Steel parts black oxidized.

Standards

Technical Specification

A	40
---	----

Technical Drawing

A1	47
B	7.5
D	10
D1	13
D2	14.5
H	24.5
H2	15
H3	30
H4	33.5
H1	4
Number of teeth	16
L	45
X	6

