



KIPP Clamping levers plastic grip, external thread Traffic blue Steel 5.8/plastic Black oxide M10X65X35

Article number	58102.100.035
Brand	-
UBB	500689742327
UNSPSC	31162807
EAN	4059245106257
PKG. of 10	Full Box Only

Technical Parameters

Class	5.8
Color	Traffic blue
D1_MM	18mm
Material	Steel/plastic
Surface treatment	Black Oxide
Thread	Metric thread
Info	For many people the Novo-Grip clamping lever represents the key to secure and comfortable gripping. This lever provides a future-oriented and powerful solution for almost any operating and clamping problem. Material: Handle fibreglass reinforced plastic with die-cast zinc toothed ring. Steel parts grade 5.8. Version: Steel parts black oxidized.

Standards

Technical Specification

A	65
---	----

Technical Drawing

A1	75
B	9.5
D	13.5
D1	18
D2	19.5
H	28.5
H2	17.5
H3	41.5
H4	45.5
H1	6.5
Number of teeth	20
L	35
X	10

