



**KIPP Clamping levers plastic grip, external thread Orange  
Stainless steel 1.4305/plastic  
M8X65X20**

Article number	58106.080.020
Brand	-
UBB	500689757838
UNSPSC	31162807
EAN	4059245111503
PKG. of 5	Full Box Only

**Technical Parameters**

Color	Orange
D1_MM	18mm
Material	Stainless steel/ plastic
Material technical	1.4305
Thread	Metric thread

Info	For many people the Novo-Grip clamping lever represents the key to secure and comfortable gripping. This lever provides a future-oriented and powerful solution for almost any operating and clamping problem. Material: Handle fibreglass reinforced plastic with die-cast zinc toothed ring. Steel parts stainless steel 1.4305. Version: Steel parts bright.
------	---

**Standards**

**Technical Specification**

A	65
A1	75

**Technical Drawing**

B	9.5
D	13.5
D1	18
D2	19.5
H	28.5
H2	17.5
H3	41.5
H4	45.5
H1	6.5
Number of teeth	20
L	20
X	8

