



KIPP Clamping levers
plastic grip, external thread
Rape yellow Stainless steel
1.4305/plastic M10X80X60

Article number	58112.101.060
Brand	-
UBB	500689779048
UNSPSC	31162807
EAN	4059245112548
PKG. of 4	Full Box Only

Technical Parameters

Color	Rape yellow
D1_MM	21.5mm
Material	Stainless steel/ plastic
Material technical	1.4305
Thread	Metric thread

Info

For many people the Novo-Grip clamping lever represents the key to secure and comfortable gripping. This lever provides a future-oriented and powerful solution for almost any operating and clamping problem. Material: Handle fibreglass reinforced plastic with die-cast zinc toothed ring. Steel parts stainless steel 1.4305. Version: Steel parts bright.

Standards

Technical Specification

A	80
A1	91.5

Technical Drawing

B	11
D	16
D1	21.5
D2	23
H	37
H2	24
H3	53.5
H4	58
H1	10
Number of teeth	22
L	60
X	10

