



KIPP Clamping levers
plastic grip, external thread
Rape yellow Stainless steel
1.4305/plastic M16X110X30

Article number	58112.160.030
Brand	-
UBB	500689779618
UNSPSC	31162807
EAN	4059245113156
PKG. of 3	Full Box Only

Technical Parameters

Color	Rape yellow
D1_MM	30mm
Material	Stainless steel/ plastic
Material technical	1.4305
Thread	Metric thread

Info	For many people the Novo-Grip clamping lever represents the key to secure and comfortable gripping. This lever provides a future-oriented and powerful solution for almost any operating and clamping problem. Material: Handle fibreglass reinforced plastic with die-cast zinc toothed ring. Steel parts stainless steel 1.4305. Version: Steel parts bright.
------	---

Standards

Technical Specification

A	110
A1	126

Technical Drawing

B	15.5
D	23
D1	30
D2	32.5
H	49
H2	33
H3	72
H4	77
H1	12
Number of teeth	26
L	30
X	16

