



KIPP Cam levers, external thread Black Stainless steel 1.4305, plastic grip M6X30

Article number	58121.060.030
Brand	-
UBB	500689945862
UNSPSC	31162807
EAN	4059245209583
PKG. of 4	Full Box Only

Technical Parameters

Color	Black
D1_MM	18.1mm
Material	Stainless steel
Material technical	1.4305
Thread	Metric thread

Info	Material: Handles and thrust washer plastic PA 66 fibreglass reinforced. Hinge pins stainless steel 1.4305. Studs and washer steel stainless steel 1.4305.Version: Handles and thrust washer black. Hinge pins, bright. Studs and washer bright stainless steel.Note: Adjustable cam levers are used if the position of the lever relative to the axis of tension only permits one specific position (interference circle). The exact position of the lever is adjusted using a screwdriver on the fine thread setscrew.
------	--

Standards

Plastics are subject to creeping under load (retardation), this can cause reduced clamping force. Drawing reference: 1) setscrew for fine adjustment of lever.adjustable

Technical Specification

A	71.5
A1	79.6
B	22
B1	16
Hand force FH (N)	125
D	6
D1	18.1
D2	9
F	2.5
H	14
H1	23.4
L	30
S	1.15

Technical Drawing

