



**KIPP Clamping levers flat,
external thread Orange
Die cast zinc/steel 5.8
Plastic coated/black oxide
M10X65X45**

Article number	58125.100.045
Brand	-
UBB	500689956331
UNSPSC	31162807
EAN	4059245086962
PKG. of 5	Full Box Only

Technical Parameters

Class	5.8
Color	Orange
D1_MM	18.5mm
Material	Die cast zinc/steel
Surface treatment	Plastic coated/black oxide
Thread	Metric thread
Info	Material: Handle die-cast zinc EN 12844. Steel parts grade 5.8.Version: Handle plastic coated. Steel parts black oxidized.

Standards

Technical Specification

A	65
A1	74.5
B	10.1
D	13.5
D1	18.5
D2	19.1
H	28.5
H2	17.8

Technical Drawing

H3	29.2
H4	32.2
H1	6.5
Number of teeth	20
L	45
X	10

