



**KIPP Clamping levers,
external thread Ruby red
Steel 1.0401/5.8 Plastic
coated M10X65X20**

Article number	58134.100.020
Brand	-
UBB	500689983897
UNSPSC	31162807
EAN	4059245083121
PKG. of 4	Full Box Only

Technical Parameters

Class	5.8
Color	Ruby red
D1_MM	18.5mm
Material	Steel
Material technical	1.0401
Surface treatment	Plastic coated
Thread	Metric thread
Info	Material: Handle 1.0401. All other steel parts grade 5.8.Version: Handle plastic coated, fine-textured structure. Steel parts black oxidized.Drawing reference: 1) flat point DIN 78.

Standards

Technical Specification

A	65
A1	74.5
B	9.5
D	13.5
D1	18.5
D2	19

Technical Drawing

H	28.5
H2	17.5
H3	42.5
H4	45.5
H1	6.5
Number of teeth	20
L	20
X	10

