



KIPP Cam levers, external thread Steel/stainless steel M10X50

Article number	58138.100.050
Brand	-
UBB	500689996014
UNSPSC	31162807
EAN	4059245209767
PKG. of 2	Full Box Only

Technical Parameters

D1_MM	27.1mm
Material	Steel/stainless steel
Thread	Metric thread

Info	Material: Handle steel 1.0401. Thrust washer plastic PA 66 GF 35-X fibreglass reinforced. Hinge pin stainless steel 1.4305. Stud and washer steel, grade 5.8.Version: Handle, stud and washer, zinc plated, blue passivated. Thrust washer black. Hinge pin bright.Note: Adjustable cam levers are used if the position of the lever relative to the axis of tension only permits one specific position (interference circle). The exact position of the lever is adjusted using a screwdriver on the fine thread setscrew. Plastics are subject to creeping under load
------	---

Standards

Technical Specification

A	96
A1	108
B	33.3
B1	24
Hand force FH (N)	350
D	10
D1	27.1
D2	11
F	8
H	18
H1	28.5
L	50
S	1.5

Technical Drawing

